

MERYDOM E.1200.20.00.C

Reviewed by MERYDOM Engineering Department. Final application approval must confirm loads, duty cycle, mounting rigidity, bolt capacity, lubrication and operating conditions.

REFERENCE

Torriani Gianni E.1200.20.00.C


STRUCTURE

Esferas de contato de quatro pontos

OVERALL ID
984 mm

Engrenagem externa

Published Technical Drawing



e_20_c-drawing.webp

Complete Product Data

All values below are generated from the current public verified replacement record. Source values are retained and metric references are shown where available.

MERYDOM CERTIFIED PRODUCT	
Product brand	MERYDOM
MERYDOM model	E.1200.20.00.C
Certified interchangeable with	Torriani Gianni E.1200.20.00.C
Verification status	Level 3 - MERYDOM Engineering Verified
Reviewed by	MERYDOM Engineering Department
Public record UID	WGRL4JHKADUL3HALLFZJ2PWUSS
MATERIALS	
Configurable ring material options	42CrMo / 50Mn
Seal material	NBR - Nitrile rubber
Configurable spacer material options	Engineering nylon / Brass
IDENTIFICATION	
Reference brand	Torriani Gianni
Reference series	E_20_C Series
Reference model	E.1200.20.00.C
Bearing structure	Esferas de contato de quatro pontos
Gear arrangement	Engrenagem externa
DIMENSION	
Overall outside diameter (Da)	1.198,4 mm
Torriani catalogue dimension B (B)	1.095,5 mm
Torriani catalogue dimension U (U)	1.092,5 mm

Complete Product Data

All values below are generated from the current public verified replacement record. Source values are retained and metric references are shown where available.

DIMENSION (CONTINUED)	
Torriani catalogue dimension C (C)	1.055 mm
Overall inside diameter (Di)	984 mm
Mass (Kg)	82 kg
MOUNTING	
Outer ring bolt circle (La)	1.135 mm
Outer ring mounting-hole count (na)	22
Inner ring bolt circle (Li)	1.012 mm
Inner ring mounting-hole count (ni)	20
GEAR	
Gear pitch diameter (P)	1.184 mm
Gear module (m)	8 mm
Gear tooth count (z)	148
PERFORMANCE	
Normal tooth force (Fz_normal)	17,6 kN
Maximum tooth force (Fz_max)	35,2 kN
PERFORMANCE RATINGS	
Rating Tooth Force Normal	17,6 kN Not simultaneous with other listed dynamic ratings
Rating Tooth Force Max	35,2 kN Not simultaneous with other listed dynamic ratings
MOUNTING INTERFACES	
Outer ring mounting	22 holes -


Complete Product Data

All values below are generated from the current public verified replacement record. Source values are retained and metric references are shown where available.

MOUNTING INTERFACES (CONTINUED)	
Inner ring mounting	20 holes -
GEAR INTERFACE	
Pitch system	module
Module reference	8 mm
Number of teeth	148
SOURCE TRACEABILITY	
Source document code	TORRIANI_GIANNI_BALL_BEARINGS_CATALOG
Source file	catalogo-torriani-cuscinetti-a-sfere.pdf
PDF page	20
Printed page	20
Source language	IT-EN
Original unit system	Metric
PUBLISHED TECHNICAL MEDIA	
Load Curve Chart	e_20_c-static-load-curve.webp SHA-256: 8c924385c556caae900d58135c7c3bbc25acc2827f2cc4a953deb2daad8049fe
Outline Drawing	e_20_c-drawing.webp SHA-256: 079addb489baf3e9ed9b1fae696966a3637ab67ad989bc321fb1d994c517f48d

Published Load / Performance Chart

Use the published chart as a preliminary selection aid only. The model legend, curve family and source document must be reviewed together with the operating load case.



e_20_c-static-load-curve.webp | SHA-256: 8c924385c556caae900d58135c7c3bbc25acc2827f2cc4a953deb2daad8049fe

Engineering note: final approval must also consider mounting rigidity, bolt capacity, duty cycle, lubrication, temperature, environment and installation conditions.

Source and Verification Traceability

PUBLIC RECORD UID

WGRL4JHKADUL3HALLFZJ2PWUSS

SOURCE FILE

catalogo-torriani-cuscinetti-a-sfere
.pdf

VERIFICATION

Level 3 - MERYDOM Engineering
Verified

SOURCE DOCUMENT

TORRIANI_GIANNI_BALL_BEARINGS_CATALOG

SOURCE LOCATION

PDF page 20 | Printed page 20

REVIEWED BY

MERYDOM Engineering Department

Engineering Confirmation Boundary

- 1 Confirm the exact model designation and all installation-envelope dimensions.
- 2 Confirm mounting-hole quantity, bolt circle, hole specification, bolt grade and preload.
- 3 Confirm gear arrangement, pitch system, tooth count, backlash and mating-pinion data.
- 4 Confirm axial, radial and moment loads, load combinations, duty cycle and required life.
- 5 Confirm support flatness and stiffness, lubrication, sealing, temperature and environment.
- 6 Final drawing revision, manufacturing tolerances and documentation package are confirmed with the quotation.

Request Price, Delivery and Final Engineering Confirmation

Email: jovi@merydom.com | Email: andi@merydom.com | WhatsApp: +86 17705201170

Product page: <https://rotnex.com/pt/produtos/rolamentos-de-giro-de-substituicao/torriani-gianni/e-1200-20-00-c/>

Trademark and legal notice: referenced brand and model names are used only for identification and cross-reference. MERYDOM is an independent manufacturer and is not affiliated with or endorsed by the referenced brand unless expressly stated.